















Quooker®	Quooker Taps											
												
	Fusion/Classic 3 in 1	Fusion/Classic 4 in 1	Fusion/Classic 5 in 1	Fusion 3 in 1	Fusion 4 in 1	Fusion 5 in 1	Flex 3 in 1	Flex 4 in 1	Flex 5 in 1	Front 3 in 1	Front 4 in 1	Front 5 in 1
Space required behind tap for lever operation	15mm	15mm	15mm	15mm	15mm	15mm	15mm	15mm	15mm	15mm	15mm	15mm
Number of sockets required	1	1	2	1	1	2	1	1	2	1	1	2
600 Sink Base	✓	✓	✓*	✓	✓	✓*	✓	✓	✓*	✓	✓	✓*
800 Sink Base	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
1000 sink base	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓*	✓	✓
Single Belfast Sink Base	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*
Double Belfast Sink Base	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*
With Sink Drawers	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*
With Working Drawer Line (not dummy)	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*	✓*

	Compatible
---	------------

	Compatible if Pro3 Tank / Cube can be placed in adjacent cabinet no more than 500mm away from the Tap
---	---